

PlastiKote Industrial Fluorescent 400 ml

Technical Information



PlastiKote Industrial Fluorescent spray paints give a lacquer-based fluorescent coating for identification and safety applications. Our Industrial Fluorescent spray paint is formulated at the highest pigmentation levels possible to provide maximum visibility in safety situations. Bright, vivid colours ensure that markings can be seen clearly - essential for marking equipment, exits, doorways and height hazards for safety or directional purposes. The lacquer based paint is durable and long-lasting, and easier to apply than traditional paint with a brush or roller. Our fast-drying formula also makes it quick and easy to mark important areas, and paint can be re-coated at any time.

Ord.-no: 440775, 440776, 440797, 440798

Quality & properties

Bright, vivid colours
Re-coat anytime
Fast-drying
High visibility
Ideal for the industrial environments

Physical & chemical data

Base: Alkyd resin
Colourname:

- Green
- Red
- Yellow
- Orange

Degree of gloss: gloss GU
Efficiency: 400 ML – 2,23 m²
Dry to touch: 15 - 20 min
Dust dry: 5-10 min
Completely dry: 1 h
Overcoatable: 1 h
Surfaces: concrete, glass, metal and wood
Minimum Working Temperature: 10 °C
Maximum Working Temperature: 25 °C
Content: 400 ML

How to use

Before use, carefully read the directions on the packaging and act accordingly. The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface. The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 10 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimeter. Apply the spray paint in several thin layers. Before applying the next layer, again shake the aerosol. When desired, after drying a primer and a lacquer can be applied. After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

As of May 7, 2025 – This release replaces all eventually earlier issued versions.