

PlastiKote Brilliant Metallic 400 ml

Technical Information



PlastiKote's Brilliant Metallic spray paint gives a gorgeously reflective, metallic finish to decorative items. It's perfect for adding a mirror-like look to photo frames, lamps, and other craft projects. Suitable for use on everything from wood and paper to glass, metal, stone, and more.

Suitable for use on most surfaces, our Brilliant Metallic spray paint instantly transforms drab to fab! With great coverage and a semi-gloss finish, why not liven up your interior design with a metallic look? Best of all, our Brilliant Metallic spray paint is touch dry in 10 minutes, and thoroughly dry in 2 hours.

Ord.-no: 440160, 440162, 440161

Quality & properties

Multi-propose
Deep rich metallic finish
Fast-drying
Durable gloss
Very good coverage

Physical & chemical data

Base: Acrylic resin
Colourname:

- Gold
- Copper
- Silver

Degree of gloss: gloss GU
Efficiency: 400 ML – 1,5 m²
Dry to touch: 10-20 min
Dust dry: 5-10 min
Completely dry: 60 min
Overcoatable: Anytime min
Surfaces: wood, metal, aluminium, glass, stone and various types of plastic
Minimum Working Temperature: 10 °C
Maximum Working Temperature: 25 °C
Flash point: n.a.
Content: 400 ML

How to use

Before use, carefully read the directions on the packaging and act accordingly.
The surface should be clean, dry and free of grease. Remove loose old lacquer and rust and sand the surface.
The surface should be clean, dry and free of grease. The aerosol should have room temperature. Best processing temperature 10 to 25°C. Before use, shake the aerosol for 2 minutes and spray a sample. Distance to the surface to be treated approximately 25 to 30 centimeter.
Apply the spray paint in several thin layers. Before applying the next layer, again shake the aerosol. When desired, after drying a primer and a lacquer can be applied.
After use, clean the valve (turn aerosol upside down and press the nozzle for approximately 5 seconds).

Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

As of May 7, 2025 – This release replaces all eventually earlier issued versions.